






## METAL CABINETS FOR FIRE EXTINGUISHER



Metal cabinets for fire extinguishers are used to store and secure fire extinguishers.

### Standard execution:

- Cabinets made of steel sheet [lacquered with Facade type polyester powder paint](#). Full door. The cabinets are properly marked with the sign "Fire extinguisher". The standard color is red (RAL 3000) and white (RAL 9003)
- PATENT or EURO lock



Fire extinguisher	Symbol	Dimensions [mm] (height x width x depth)
Fire extinguisher 2 kg	S-SG-2	430 x 200 x 200
Fire extinguisher 4 kg or 6 kg	S-SG-6	600 x 250 x 200
Fire extinguisher 12 kg or carbon-dioxide fire extinguisher GS 5 kg	S-SG-12	800 x 300 x 250



Fire extinguisher	Symbol	Dimensions [mm] (height x width x depth)
Fire extinguisher 2 x 6 kg	S-SG-6X2	600 x 500 x 200
Fire extinguisher 2 x 12 kg or carbon-dioxide fire extinguisher GS 5 kg	S-SG-12X2	800 x 500 x 250



Fire extinguisher	Symbol	Dimensions [mm] (height x width x depth)
Fire extinguisher 3 x 6 kg	S-SG-6X3-Z	600 x 700 x 200
Fire extinguisher 3 x 12 kg or carbon-dioxide fire extinguisher GS 5 kg	S-SG-12X3-Z	800 x 750 x 250

Inquiries about other execution options should be directed to the e-mail address: [handlowy@supron.pl](mailto:handlowy@supron.pl)

## POSSIBILITY OF IMPLEMENTATION



**CABINET WITH FRAME**

Installation in recess, frame flush with the wall



**GALVANIZED STEEL SHEET**

Lacquered with **Facade** type polyester facade



**INOX**

Stainless steel type 304 with 240 cut or 316L. In



**SAFETY GLASS**

Door with matt or transparent glass. Any graphic

paint. Solution resistant to atmospheric condition and UV radiation

aggressive environment (e.g. swimming pools) recommended is only 316L steel

can be used



#### PLEXI WINDOW

Window in door protected by plexi



#### INDIVIDUAL COLOR

Any color from RAL pallet



#### NON-STANDARD DIMENSIONS

Possible to adopt dimensions to customer request

## TYPE OF LOCK



#### PATENT LOCK

Large quantity of cabinets can be opened with one key. The key for emergency opening is located behind the safety glass.



#### EURO LOCK

Twist lock adapted to put seal on.